




使用温度范围 (Ambient temperature Range): $-25^{\circ}\sim+85^{\circ}$

适用线规 (Applicable Wires):AWG 26#~22#

适用基板厚度 (Applicable PCboard thickness):1.6mm

额定电压 (Voltage rating):250V AC,DC

额定电流 (Current rating):3A

接触电阻 (Contact Resistance): $\leq 0.01\Omega$

绝缘电阻 (Insulation Resistance): $\geq 1000M\Omega$

耐压 (Withstand Voltage):1000V/min

材料 (Material)

1.基座: PA66 FV2

孔位	A	B
2510-2Y	2.54	5.74
2510-3Y	5.08	8.28
2510-4Y	7.62	10.82
2510-5Y	10.16	13.36
2510-6Y	12.70	15.90
2510-7Y	15.24	18.44
2510-8Y	17.78	20.98
2510-9Y	20.32	23.52
2510-10Y	22.86	26.06
2510-11Y	25.40	28.60
2510-12Y	27.94	31.14
2510-13Y	30.48	33.68
2510-14Y	33.02	36.22
2510-15Y	35.56	38.76
2510-16Y	38.10	41.30

2					
1		Housing 基座	PA66 94V-0	1	White 白色
序号	图号	名称	材料	数量	附注
未注公差		 韩下® 深圳市韩下电子有限公司			
X.°±3° X.X°±5°					
>0-3	>3-18	>18-50	>50-120		
±0.12	±0.15	±0.3	±0.5	MMOnly	——
				Design Units	SIZE
				METRIC	A4
制作		审核	批准	材料	图号
					Part No.
黄彬	张伟	罗小春	见图解	品名	HX-2510-3Y