





技术参数 SPECIFICATIONS

- 1.线数 (Poles) : 2~12
- 2.适用线规 (Applicable wires) : AWG18#~24#
- 3.适应基板厚度 (Applicable PC board thickness) : 1.6mm~2.0mm
- 4.温度范围 (Temperature range) : -25 ~85
- 5.额定电压 (Voltage rating) : 250V.Ac/Dc
- 6.额定电流 (Current rating) : 8A
- 7.接触电阻 (Contact resistance) : ≤0.015Ω
- 8.绝缘电阻 (insulation resistance) : ≥1000MΩ
- 9.耐压 (Withstand voltage) : 1500V.Ac/1min
- 10.材料 (Material) :
 - 孔座 (Housing) : 尼龙 (PA66) UL94V-0
 - 针座 (Wafer) : PA-9T UL64V-0
 - 端子 (Terminal) : 磷青铜 (Phos.bronze Tin/plated)

1				Phos Bronze tin 磷青铜镀锡		1					
序号		图号		名称		材料		数量		附注	
未注公差				 深圳市韩下电子有限公司							
X.°±3° X.X°±5°											
>0-3	>3-18	>18-50	>50-120			Design Units	SIZE				
±0.12	±0.15	±0.3	±0.5	MMOnly	——	METRIC	A4				
制作		审核		批准		材料		图号		Part No.	
黄彬		张伟		罗小春		见图解		品名		HX-5569-T	