




REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		初版发行	2018-05-28			

2X12P	51.8	46.2
2X11P	47.6	42.0
2X10P	43.4	37.8
2X9P	39.2	33.6
2X8P	35.0	29.4
2X7P	30.8	25.2
2X6P	26.6	21.0
2X5P	22.4	16.8
2X4P	18.2	12.6
2X3P	14.0	8.4
2X2P	9.8	4.2
2X1P	5.6	-
4.2-5559 PINS	DIM.A	DIM.B

适应基板厚度：1.6mm~2.0mm

温度范围：-25℃~85℃

额定电压：250V AC/DC

额定电流：8A

接触电阻：≤0.015Ω

绝缘电阻：≥1000MΩ

耐 压：1500V AC/minute

适合线规：18#~24#

技术要求：

- 1) 材质：见附表；
- 2) 电镀：见附表；
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象；
- 4) 端子表面无氧化、电镀不良等现象。

GENERAL TOLERANCES			
DIM	TOL	DIM	DEG
X.		X°	±3.00°
X.X	±0.35	X.X°	±2.00°
X.XX	±0.25	X.XX°	±1.00°
X.XXX	±0.15	X.XXX°	

1	Housing	1 PCS	材质:PA66 (UL94V-2),颜色:本色		
NO.	NAME	Q'TY	DESCRIPTION		
 韩下® 深圳市韩下电子有限公司					
DRAW :	黄彬	2018-04-22	TITLE:		DRAW NAME:
DESIGN:			HX-5569-2x2Y		胶壳
CHECK:	张伟	2018-04-22	SERIES: 4.2 SERIES		DRAW NO.
APPROVED	罗小春	2018-04-22	P/N:		
CUSTOMER DRAWING			REV. 1.00	SCALE N/A	UNIT: mm
					SHEET: 1/1
					