


P.C.B Layout (copper-sided view)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

② Terminal	4	Phosphor bronze	Sn Plating				
① Housing	1	PPA	Black				
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK	
APPROVALS		DATE					
DRAWN	LIUCAN	2023.3.16					TITLE:
CHECKED				PART NO.	PJ-327C		
APPROVALS				TOLERANCES ARE	ANGLE	UNIT: mm	
		30~以上:	±0.30	±2'	SCALE: 1:1	PROJ:	
		10~30	±0.20				
		5~10	±0.15				
		~ 5	±0.10				
ECN NO.	REV.	DATE.	NEW DESCRIPTION.	CHANGE.	CHECK.	APPRO.	SHEET 1 OF 1