




尺寸(mm)			
孔位	A	B	C
2X2	6.0	2.0	4.5
2X3	8.0	4.0	6.5
2X4	10.0	6.0	8.5
2X5	12.0	8.0	10.5
2X6	14.0	10.0	12.5
2X7	16.0	12.0	14.5
2X8	18.0	14.0	16.5
2X9	20.0	16.0	18.5
2X10	22.0	18.0	20.5
2X11	24.0	20.0	22.5
2X12	26.0	22.0	24.5
2X13	28.0	24.0	26.5
2X14	30.0	26.0	28.5
2X15	32.0	28.0	30.5
2X16	34.0	30.0	32.5

- 1.工作温度: -25°C~85°C.
- 2.适用线规: AWG#26~#22.
- 3.额定电压: 250V DC/AC(rms).
- 4.额定电流: 2.0A.
- 5.接触电阻: $\leq 20m\Omega$.
- 6.耐压值: 800V AC/minute.
- 7.绝缘电阻: $\geq 1000M\Omega$.

技术要求:

- 1) 材质: 见附表;
- 2) 电镀: 见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。

GENERAL TOLERANCES			
DIM TOL		DIM	DEG
X.		X°.	±3.00°
X.X	±0.35	X.X°	±2.00°
X.XX	±0.25	X.XX°	±1.00°
X.XXX	±0.15	X.XXX°	

REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		行发版初	2018-04-22			

1	Housing	1 PCS	材质:PA66 (UL94V-0),颜色:本色			
NO.	NAME	Q'TY	DESCRIPTION			
 韩下® 深圳市韩下电子有限公司						
DRAW :	黄彬	2018-04-22	TITLE:		DRAWNAME:	
DESIGN:			压线端子胶壳		HX-PHD2.0-2x6Y	
CHECK:	张伟	2018-04-22	SERIES: 2.5XHB SERIES		DRAWNO.	
APPROVED	罗小春	2018-04-22	P/N:		UNIT:	SHEET:
CUSTOMER DRAWING			REV. 1.00	SCALE N/A	mm	1/1
					+ 	
D		E			F	