




| REV. | EC# | DESCRIPTION | DATE       | DRAWN | CHECK | APPROVED |
|------|-----|-------------|------------|-------|-------|----------|
| 1.00 |     | 初版发行        | 2018-05-28 |       |       |          |
|      |     |             |            |       |       |          |
|      |     |             |            |       |       |          |

|               |       |       |
|---------------|-------|-------|
| 2X12P         | 51.8  | 46.2  |
| 2X11P         | 47.6  | 42.0  |
| 2X10P         | 43.4  | 37.8  |
| 2X9P          | 39.2  | 33.6  |
| 2X8P          | 35.0  | 29.4  |
| 2X7P          | 30.8  | 25.2  |
| 2X6P          | 26.6  | 21.0  |
| 2X5P          | 22.4  | 16.8  |
| 2X4P          | 18.2  | 12.6  |
| 2X3P          | 14.0  | 8.4   |
| 2X2P          | 9.8   | 4.2   |
| 2X1P          | 5.6   | -     |
| 4.2-5559 PINS | DIM.A | DIM.B |

适应基板厚度：1.6mm~2.0mm  
温度范围：-25℃~85℃  
额定电压：250V AC/DC  
额定电流：8A  
接触电阻：≤0.015Ω  
绝缘电阻：≥1000MΩ  
耐 压：1500V AC/minute  
适合线规：18#~24#

- 技术要求：
- 1) 材质：见附表；
  - 2) 电镀：见附表；
  - 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象；
  - 4) 端子表面无氧化、电镀不良等现象。

| GENERAL TOLERANCES |       |        |        |
|--------------------|-------|--------|--------|
| DIM                | TOL   | DIM    | DEG    |
| X.                 |       | X°     | ±3.00° |
| X.X                | ±0.35 | X.X°   | ±2.00° |
| X.XX               | ±0.25 | X.XX°  | ±1.00° |
| X.XXX              | ±0.15 | X.XXX° |        |

|                                                                                                                                             |         |            |                         |            |                                                                                       |
|---------------------------------------------------------------------------------------------------------------------------------------------|---------|------------|-------------------------|------------|---------------------------------------------------------------------------------------|
| 1                                                                                                                                           | Housing | 1 PCS      | 材质:PA66 (UL94V-2),颜色:本色 |            |                                                                                       |
| NO.                                                                                                                                         | NAME    | Q'TY       | DESCRIPTION             |            |                                                                                       |
| <div><div> 韩下 HANXIA</div><div>深圳市韩下电子有限公司</div></div> |         |            |                         |            |                                                                                       |
| DRAW :                                                                                                                                      | 黄彬      | 2018-04-22 | TITLE:<br>HX-5569-2x5Y  |            | DRAW NAME:<br>胶壳                                                                      |
| DESIGN:                                                                                                                                     |         |            | SERIES: 4.2 SERIES      |            |                                                                                       |
| CHECK:                                                                                                                                      | 张伟      | 2018-04-22 | P/N:                    |            | DRAW NO.                                                                              |
| APPROVED                                                                                                                                    | 罗小春     | 2018-04-22 | REV. 1.00               |            | UNIT: mm                                                                              |
| CUSTOMER DRAWING                                                                                                                            |         |            | SCALE N/A               | SHEET: 1/1 |  |