






SPECIFICATION

1. Rating : DC 30V 2A.
2. Contact resistance: $\leq 50\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
4. Withstanding voltage: 500VAC .
5. Insertion and extraction force: 3-30N.
6. life test: 5,000 cycles.
7. Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
8. Sign"* "is importance dimension.

电话: 0769-82310511-867

邮箱: hooya89@hooya.hk

PIN	#2.0	#2.5
APPD.	✓	



				TOLERANCE UNLESS SPECIFIED							
				<1.5: ±0.1mm	ANGULAR	A0	2025.10.22	首次发行		LP	
				>1.5~5.0: ±0.25mm	±1°	NO	DATE	REVISIONS		BY	APPD
5	CASE	PPA	1	>5.0: ±0.3mm		TITLE: DC JACK		UNIT : MM	ROHS COMPLIANT	DWN	
4	PIN	BRASS	1	MODEL: DC-022F#2.5-PU-09		SCALE: 1:1		CHK'D			
3	SPRING	PHOSPHOR BRONZE	1	DONGGUANG HAOYU ELECTRONICS CO., LTD		APPD					
2	SLEEVE	BRASS	1	皓宇 HOOYA 东莞市弘皓电子有限公司		PRO.AGL: 		REV: A0			
1	HOUSING	PA66	1								
NO.	PART	NAME	MATERIAL	QTY	FINISHING						