


SCHEMATIC



SPECIFICATION

1. Rating : DC 30V 0.5A.
2. Contact resistance: $\leq 50\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
4. Withstanding voltage: 500VAC .
5. Insertion and extraction force: 3-20N.
6. life test: 5,000 cycles.
7. Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
8. Sign "*" is importance dimension.

Tel : 0769-82310511-867

					TOLERANCE UNLESS SPECIFIED								
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°							
							NO	DATE	REVISIONS			BY	APPD
2	TERMINAL 2#	PHOSPHOR COPPER	1	Au-PLATED	TITLE: DC JACK				UNIT : MM	ROHS	DWN		
3	SPRING	BERYLLIUM COPPER	3	Au-PLATED	MODEL: PJ-309B-09				SCALE: 1:1	COMPLIANT	CHK'D		
2	TERMINAL 1#	PHOSPHOR COPPER	2	Au-PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司				APPD		PRO.AGL:  		REV :A0
1	HOUSING	PC	1	BLACK									
NO.	PART NAME	MATERIAL	QTY	FINISHING									