








SCHEMATIC




P.C.B LAYOUT




SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: ≤500mΩ.
- 3.Insulation resistance: ≥100MΩ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: 30±20gf.
- 6.life test: 100000 cycles.
- 7.Operation temperature range:-25℃~85℃.
- 8.Travel: 0.3^{+0.3}_{-0.2}mm
- 9.Sign"* "is importance dimension.



					TOLERANCE UNLESS SPECIFIED										
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°									
5	TERMINAL	PHOSPHOR COPPER	4	Ag PLATED			NO	DATE	REVISIONS			BY	APPD		
4	CASE	LCP	1	BLACK	TITLE:TACT SWITCH				UNIT : MM	ROHS	DWN				
3	SPRING	PHOSPHOR COPPER	1	Au PLATED	MODEL:TC-0721C-08				SCALE: 1:1	COMPLIANT	CHK'D				
2	COVER	SUS	1	NATURAL	 皓宇 HOOYA				DONGGUANG HAOYU ELECTRONICS CO., LTD				APPD		
1	BUTTON	LCP	1	OFF-WHITE					东莞市弘皓电子有限公司				PRO.AGL: 		
NO.	PART NAME	MATERIAL	QTY	FINISHING											




REEL
SCALE 1:10



示意图仅供参考



CARRIER TAPE



COVER TAPE

8					DRAWING (制图)	CHECKED (审核)	APPROVED (核准)	MATERIAL (材质)	TOLERANCES (一般公差)				
								SEE NOTE	TOLERANCE UNLESS SPECIFIED: ±0.3		X. ±3.0° .X ±2.0° .XX ±1.0°		
								COLOR (颜色)	TITLE (品名)		TACT SWITCH 包装示意图		
								SEE NOTE					
	X1							FINISH (后处理)	DWG NO. (图号)		TC-0721C-08		
	REV (版本)	ECN NO. (ECN编号)	DATE (日期)	DRAWING (制图)	APPROVED (核准)			SEE NOTE	PROJECTION (製角)	UNITS (單位)	SCALE (比例)	SHEET (張數)	REV (版本)
	A	B		C		D	E	F	G		H		
										MM	N/A	1/1	X1