






SPECIFICATION

1. Rating : DC 30V 2A.
2. Contact resistance: $\leq 50\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
4. Withstanding voltage: 500VAC .
5. Insertion and extraction force: 3-30N.
6. life test: 5,000 cycles.
7. Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
8. Sign"* "is importance dimension.

电话: 0769-82310511-867

邮箱: hooya89@hooya.hk

PIN	#2.0	#2.5
APPD.	✓	



				TOLERANCE UNLESS SPECIFIED							
				<1.5: $\pm 0.1\text{mm}$	ANGULAR	A0	2025.10.22	首次发行		LP	
				>1.5~5.0: $\pm 0.25\text{mm}$	$\pm 1^{\circ}$	NO	DATE	REVISIONS		BY	APPD
5	CASE	PPA	1			TITLE: DC JACK		UNIT : MM	ROHS COMPLIANT	DWN	
4	PIN	BRASS	1	CuSn-PLATED		MODEL: DC-022F#2.0-PU-09		SCALE: 1:1	CHK'D		
3	SPRING	PHOSPHOR BRONZE	1	CuSn-PLATED		DONGGUANG HAOYU ELECTRONICS CO., LTD			APPD		
2	SLEEVE	BRASS	1	CuSn-PLATED		皓宇 HOOYA 东莞市弘皓电子有限公司					
1	HOUSING	PA66	1								
NO.	PART	NAME	MATERIAL	QTY	FINISHING			PRO.AGL:			REV: A0