


	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2024.11.11	
A2	N/A			2026.03.09	

PART NO.:

X9127 W H-10 S1-PT RE

Series No

Category:W—Wafer

Welding Board Angle:H-Connect wires

Row No-Pin No:XX-04P~26P

Special No.:S1—With grooves and edges

Material:PT-PBT UL94V-0

Color: RD—purplish red

RE-Red Color

Poles	Dimensions(mm)	
	A	B
04	8.45	2.54
06	10.99	5.08
08	13.53	7.62
10	16.07	10.16
12	18.61	12.70
14	21.15	15.24
16	23.69	17.78
18	26.23	20.32
20	28.77	22.86
22	31.31	25.40
24	33.85	27.94
26	36.39	30.48

■ SPECIFICATIONS

- Voltage rating:500V AC/DC
- Current rating:1A AC/DC
- Withstanding Voltage:1000V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance: $\geq 1000M\Omega$
- Contact resistance $\leq 20m\Omega$
- After environment testing $\leq 30m\Omega$

X9127WH-10S1-PTRE		Red	PBT UL 94V-0	Brass	Tin-Plated
X9127WH-10S1-PTRD		purplish red			
PART NO		Color	Material	Material(Pin)	Finish(Pin)
	DESIGN		VIEW: 	MODEL TYPE: 1.27mm Crimp Style Connector	
	CHECKED		UNIT: mm/in	PART NO.: X9127WH-10S1-PTRE	
	APPROVED		SIZE: A4	DWG NO.:	
INDUSTRIAL PRECISION CO.,LIMITED				SCALE N/A	PAGE 1/1
				REVISION A2	

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED	TOLERAUCES

XK13 星城 Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED