






REACH & RoHS
COMPLIANT



REV.	ECN / DESCRIPTION	BY	DATE
A0	NEW	X.YAN	2025.01.22



1. SPECIFICATION:

- 1.1. CURRENT RATING: 0.5A Max.
- 1.2. VOLTAGE RATING: 30V_{ac} (r.m.s) Max.
- 1.3. CONTACT RESISTANCE: 40mΩ Max.
- 1.4. INSULATION RESISTANCE: 100MΩ Min.
- 1.5. DIELECTRIC WITHSTANDING VOLTAGE:
AC 500V Min. 1 minute
- 1.6. OPERATION TEMPERATURE RANGE: -25° C ~ 85° C

2. MECHANICAL

- 2.1. INSERTION FORCE: 4.5KGF MAX
- 2.1. WITHDRAWAL FORCE: 1.0KGF MIN
- 2.3. DURABILITY: 5000 CYCLES

3. MATERIALS

- 3.1. HOUSING MATERIAL: Temperature Plastic, UL94V-0.
- 3.2. CONTACT MATERIAL: Copper Alloy
- 3.3. SHIELD: SPCC

CND-tek
磁联达

深圳磁联达电子有限公司
Shenzhen magnetic Lianda Electronics Co., LTD

Address: 505, West Block, No. 221, Niucheng Road, Niucheng Village, Baiwang
Community, Xili Street, Nanshan District, Shenzhen
E-mail: sales1@cd-tek.com 0755-27652992 29016433 Website: www.cd-tek.com

TITLE:
HDMI-19P 四脚插件铁无点

PART NO.:
HDMI-19P-CND

REMARK:


SIZE
A4

SACLE
1:1

SHEET
1/1

UNITS
MM[INCH]

REV
A0



GENERAL TOLERANCES
UNLESS SPECIFIED

x0.35	x0.8.0
x0.30	x0.2.0
.xx0.25	.xx0.1.5
.xxx0.10	.xxx0.1.0

APPROVED BY:
QG.CHEN

CHECKED BY:
SL.WANG

DESIGN BY:
X.YAN