




CHIP COMMON MODE CHOKE

High Common Mode Impedance at High Frequency.
Excellent Noise Suppression Performance.
Small Size and Low Profile, Surface Mount Type.
Operating Temperature Range: -40 ℃ to +85 ℃.
RoHS Compliant.


Electrical Specifications@25℃

Part Number	Common mode Impedance (ohm ±25%@100M)	DCR (Ω Max)	Rated Current mA Max	Rated Volt (Vdc)	IR M(Ω Min)
03.LF.8011NZND T-CND	800	0.88	300	125	10


MECHANICAL



SCHEMATICS





IMPEDEANCE FREQUENCY



Unless otherwise specified all tolerances are:±0.25mm

TAPING AND PACKING



Dimensions in mm

Quantity (pcs):
3000 PCS PER REEL
10 REELS PER CARTON
30000 PCS PER CARTON