


REACH & RoHS
COMPLIANT

REV.	ECN / DESCRIPTION	BY	DATE
A0	NEW	X.YAN	2024.10.22



NOTES:

MATERIAE

- 1.HOUSING MATERIAL:PBT,COLOR IS YELLOW
- 2 .CONTACT MATERIAL:PHOSPHOR BRONZE 0.46mm.
- 3.PLATING:PLATING OVER NICKEL

ELECTRICAL:

- 1.VOLTAGE RATING:125 VAC RMS.
- 2.CURRENT RATING:1.5 AMP.
- 3.CONTACT RESISTANCE:30 mΩ MAX.
- 4.INSULATION RESISTANCE:500 MΩ MIN
- 5.DIELECTRIC WITHSTANDING RESISTANCE:500V AC RMS 50HZ.1MIN.

MECHANICAL:

1. DURRABILITY:750 CYCLES MIN.
- 2.PCB RETENTION PRE-SOLDER:1 LB MIN.

PART NUMBER	COLOR
R1488R56B	BLACK
R1488R56Y	YELLOW
R1488R56G	GRAY

CND-tek
磁联达

深圳磁联达电子有限公司
Shenzhen magnetic Lianda Electronics Co., LTD

Address: 505, West Block, No. 221, Niucheng Road, Niucheng Village, Baiwang Community, Xili Street, Nanshan District, Shenzhen
E-mail: sales1@cd-tek.com 0755-27652992 29016433 Website:www.cd-tek.com

TITLE: 1*4 8P8C 56B	SIZE A4	UNITS MM[INCH]	GENERAL TOLERANCES UNLESS SPECIFIED		APPROVED BY: QG.CHEN
PART NO.: R1488R56Y	SACLE 1:1	REV A0	xÑ0.35	xÑ3.0Á	CHECKED BY: SL.WANG
REMARK:	SHEET 1/1		.xÑ0.30	.xÑ2.0Á	DESIGND BY: X.YAN
			.xxÑ0.25	.xxÑ1.5Á	
			.xxxÑ0.10	.xxxÑ1.0Á	