



NOTE:
 1. Rating: 24V 25mA DC
 2. Contact Resistance: 50mΩ max
 3. Dielectric Strength: 500V AC/1Minute
 4. Operating Force: 800gf Max
 5. Operating Life: 2,000 Cycles

Position(位数)	2P	3P	4P	5P	6P	7P	8P	9P	10P	12P
DIM.A(长度)	6.64	9.18	11.72	14.26	16.80	19.34	21.88	24.42	26.96	32.04
DIM.B(长度)	2.54	5.08	7.62	10.16	12.70	15.24	17.78	20.32	22.86	27.94
PART NO.	凸柄(P)	DS-02RP	DS-03RP	DS-04RP	DS-05RP	DS-06RP	DS-07RP	DS-08RP	DS-09RP	DS-10RP
盖子/红色(R)	DS-02RS	DS-03RS	DS-04RS	DS-05RS	DS-06RS	DS-07RS	DS-08RS	DS-09RS	DS-10RS	DS-12RS
PART NO.	凸柄(S)	DS-02BP	DS-03BP	DS-04BP	DS-05BP	DS-06BP	DS-07BP	DS-08BP	DS-09BP	DS-10BP
盖子/蓝色(B)	DS-02BS	DS-03BS	DS-04BS	DS-05BS	DS-06BS	DS-07BS	DS-08BS	DS-09BS	DS-10BS	DS-12BS

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

APPROVALS		DATE	ELECTRONICS CO.,LTD	
DRAWN	G.M.Chen	2015/6/26	ELECTRONICS CO.,LTD	
CHECKED			DIP SWITCHES	
APPROVALS			DS-XXXX	
TOLERANCES ARE		30 ^{±0.15}	±0.30	ANGLE
		10 ^{±0.10}	±0.20	UNIT: mm
		5 ^{±0.10}	±0.15	SCALE: 1:1
			±2'	DRAWING NO.
				SHEET 1 OF 1
				PROJ.:

ITEM	PART NAME	QTY.	MATERIAL	FINISHING
⑤	Gum Water		Epikote	Black
④	Terminal		Phosphor bronze	Au Plating
③	Base	1	PBT	Black
②	Cover	1	PBT	Red/Blue
①	Keystoke	1	PBT	White