



REACH & RoHS
COMPLIANT

REV.	ECN / DESCRIPTION	BY	DATE
A0	NEW	X.YAN	2024.10.22



NOTES:
MATERIAE

1. HOUSING MATERIAL: GLASS FILLED POLYESTER
2. CONTACT MATERIAL: PHOSPHOR BRONZE 0.46mm.
3. PLATING: PLATING FU
4. SHIELD: 0.20mm THICKNESS COPPER ALLOY WITH NICKEL

ELECTRICAL:



1. VOLTAGE RATING: 125 VAC RMS.
2. CURRENT RATING: 1.5 AMP.
3. CONTACT RESISTANCE: 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 500 MEGOHMS MIN @ 500V DC
5. DIELECTRIC WITHSTANDING RESISTANCE: 500V AC RMS 50HZ. 1MIN.

MECHANICAL:

1. DURABILITY: 750 CYCLES MIN.
2. PCB RETENTION PRE-SOLDER: 1 LB MIN.

ENVIRONMENT AL:

1. STORAGE: -40°C ~ +85°C
2. OPERATION: -40°C ~ +85°C



PCB board Layout Top View

CND-tek
磁联达

深圳磁联达电子有限公司
Shenzhen magnetic Lianda Electronics Co., LTD

Address: 505, West Block, No. 221, Niucheng Road, Niucheng Village, Baiwang Community, Xili Street, Nanshan District, Shenzhen
E-mail: sales1@cd-tek.com 0755-27652992 29016433 Website: www.cd-tek.com

TITLE: 1x2 5JA 8P8C LED EMI	SIZE A4	UNITS MM[INCH]	GENERAL TOLERANCES UNLESS SPECIFIED		APPROVED BY: QG.CHEN
PART NO. R1288ELR5JA	SACLE 1:1	REV A0	×0.35	×0.8.0	CHECKED BY: SL.WANG
			×0.30	×0.2.0	
REMARK:	SHEET 1/1		×0.25	×0.1.5	DESIGND BY: X.YAN
			×0.10	×0.1.0	