





REACH & RoHS
COMPLIANT

REV.	ECN / DESCRIPTION	BY	DATE
A0	NEW	X.YAN	2024.10.22



NOTES:

MATERIAE

1. HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.
2. CONTACT MATERIAL: PHOSPHOR BRONZE 0.46mm.
3. PLATING: PLATING OVER NICKEL
4. SHIELD: 0.20mm THICKNESS COPPER ALLOY WITH NICKEL

ELECTRICAL:

1. VOLTAGE RATING: 125 VAC RMS.
2. CURRENT RATING: 1.5 AMP.
3. CONTACT RESISTANCE: 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 500 MEGOHMS MIN @ 500V DC
5. DIELECTRIC WITHSTANDING RESISTANCE: 1000V AC RMS 50HZ. 1MIN.

MECHANICAL:

1. DURRABILITY: 750 CLES MIN.
2. PCB RETENTION PRE-SOLDER: 1 LB MIN.

PART NUMBER	COLOR
R1488R96B	BLACK
R1488R96Y	YELLOW
R1488R96G	GRAY

CND-tek
磁联达

深圳磁联达电子有限公司
Shenzhen magnetic Lianda Electronics Co., LTD

Address: 505, West Block, No. 221, Niucheng Road, Niucheng Village, Baiwang Community, Xili Street, Nanshan District, Shenzhen
E-mail: sales1@cd-tek.com 0755-27652992 29016433 Website: www.cd-tek.com

TITLE: 1*4 8P8C 96B	SIZE A4	UNITS MM[INCH]	GENERAL TOLERANCES UNLESS SPECIFIED		APPROVED BY: QG.CHEN
PART NO.: R1488R96B	SACLE 1:1	REV A0	xÑ0.35	xÑ3.0Á	CHECKED BY: SL.WANG
REMARK:	SHEET 1/1		.xxÑ0.25	.xxÑ1.5Á	DESIGND BY:
			.xxxÑ0.10	.xxxÑ1.0Á	X.YAN