









RECOMMENDED PCB LAYOUT
TOP VIEW(.XX±0.05)

PART NO.	DIM A	DIM B
HYCW-BA3P2517T	1.7	3.05±0.2
HYCW-BA3P2520T	2.0	3.35±0.2

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

使用寿命: 5000次以上

塑件(材质): LCP(黑色) UL94-V0

接触点(材质): 锡磷青铜, 触点镀金3U",

焊脚镀金1U", 镍30-80U"

固定片(材质): 黄铜C2680,

镀全雾锡70U"以上, 镍底30-80U"

环保要求: 符合ROHS限值。



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X." ±2" X.X" ±0.5" UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.5PH 3P 正压电池座	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2604091201
			SHEET NO.	1 OF 1