

规格	DIM A	DIM B
HYCW-BF3P16127D-18	4.8	1.8
HYCW-BF4P16127D-34	6.4	3.4
HYCW-BF5P16127D-50	8.0	5.0
HYCW-BF6P16127D-66	9.6	6.6
HYCW-BF7P16127D-82	11.2	8.2
HYCW-BF8P16127D-98	12.8	9.8
HYCW-BF9P16127D-114	14.4	11.4
HYCW-BF10P16127D-130	16.0	13.0

性能:

额定电流: 3.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ






绝缘电阻: 500MΩ

工作温度: -45℃~+85℃

使用寿命: 5000次以上

塑件(材质): PA9T黑色

接触点(材质): 黄铜C2680, 镀金3U



RECOMMENDED PCB LAYOUT

TOP VIEW(.XX±0.05)



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X." ±2" X.X" ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 1.6PH 1.27H 母座有柱	
 UNIT: mm [inch]		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2603261120
SCALE:1:1	SIZE: A4			SHEET NO.	1 OF 1