








| 规格                 | DIM A | DIM B |
|--------------------|-------|-------|
| HYCW-BF2P4019D-60  | 8.0   | 6.0   |
| HYCW-BF3P4019D-100 | 12.0  | 10.0  |
| HYCW-BF4P4019D-140 | 16.0  | 14.0  |
| HYCW-BF5P4019D-180 | 20.0  | 18.0  |
| HYCW-BF6P4019D-220 | 24.0  | 22.0  |

性能:

额定电流: 5.0A

额定电压: 30V

耐电压: 500V

接触电阻: 30mΩ


绝缘电阻: 500MΩ

工作温度: -55℃~+125℃

使用寿命: 10000次以上


塑件(材质): LCP黑色

接触点(材质): 黄铜C2680, 镀金



RECOMMENDED PCB LAYOUT

TOP VIEW(.XX±0.05)



深圳市华宇创精密电子有限公司

|                                                                                                                    |                    |                      |                               |                  |
|--------------------------------------------------------------------------------------------------------------------|--------------------|----------------------|-------------------------------|------------------|
| TOLERANCE:<br>X.X ±0.30<br>X.XX ±0.25<br>X.XXX ±0.15<br>X' ±2" X.X' ±0.5"<br>UNIT: mm [inch]<br>SCALE:1:1 SIZE: A4 | DRAWN BY :<br>陈一鸣  | DATE :<br>2014-02-23 | PART NAME:<br>4.0PH 1.9H 母座带柱 |                  |
|                                                                                                                    | CHECKED BY:<br>马跃  | DATE :<br>2014-02-23 | PART NO.                      | SEE TABLE        |
|                                                                                                                    | APPROVED BY:<br>邱敏 | DATE :<br>2014-02-23 | DRAW NO:                      | HYC-202006061042 |
|                                                                                                                    |                    |                      | SHEET NO.                     | 1 OF 1           |