








RECOMMENDED PCB LAYOUT
TOP VIEW(.XX±0.05)

Pin数	PART NO.	DIM A	DIM B	DIM C
2Pin	HYCW-BB2P2050D	5.3	4.4	
3Pin	HYCW-BB3P2050D	7.3	6.4	2.0
4Pin	HYCW-BB4P2050D	9.3	8.4	4.0
5Pin	HYCW-BB5P2050D	11.3	10.4	6.0
6Pin	HYCW-BB6P2050D	13.3	12.4	8.0

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ


工作温度: -40℃~+85℃

塑件(材质): LCP E130I黑色

接触点(材质): 磷青铜C5210,
触点镀金3U"



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.0PH 5.0H 侧压电池座 有柱	
 UNIT: mm [inch]		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2604081541
SCALE:1:1	SIZE: A4			SHEET NO.	1 OF 1