








RECOMMENDED PCB LAYOUT
TOL:(±0.05)

性能:

额定电流: 5.0A

额定电压: 30V

耐电压: 500V

接触电阻: 30mΩ Max

绝缘电阻: 500MΩ Min

工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜, 触点镀金3U",

使用寿命: 10000次以上



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 4.25PH 4.75H 1P 正压电池座 有柱	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HWCW-BA1P425475D-37	MOLD NO.
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2604141123	SHEET NO. 1 OF 1