









RECOMMENDED PCB LAYOUT

TOP VIEW (.XX±0.05)

PART NO.	DIM A	DIM B
HYCW-BA4P2517T	1.70	3.05±0.2
HYCW-BA4P2520T	2.0	3.35±0.2

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜, 镀金



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.5PH 4P 正压电池座	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2604091429
				SHEET NO.	1 OF 1