









RECOMMENDED PCB LAYOUT
TOP VIEW (.XX±0.05)

规格料号	DIM A	DIM B	DIM C
HYCW-BB2P5080D-C50	8.00	5.70±0.3	6.85±0.3
HYCW-BB2P5092D-C50	9.25	6.95±0.3	8.10±0.3
HYCW-BB2P50105D-C50	10.50	8.20±0.3	9.35±0.3

性能:

额定电流: 3.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP黑色

接触点(材质): 铜合金, 触点镀金3U"



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 5.0PH 2P 侧压电池座 插件脚 有柱	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2604141514
				SHEET NO.	1 OF 1