

材料:Material:

塑胶: LCP

端子: Contact: C2680

Plated Gold in Mating Area;

Tin On Solder Talls

外壳 Shell: SPCC

寿命测试: life test:

1500次, 插拔速度300次/小时

插入力MAX: 4.5Kgf Max.

拔出力MIN: 0.45Kgf Min.

盐雾测试: 24H

特性 Specifications:

电器 Electrical:

接触阻抗: Contact Resistance

30 mΩ MAX

耐电压 Dielectric Withstanding Voltage:


500V AC

绝缘阻抗: Insulation Resistance:





1000 MΩ MIN

Working temprature: -30° TO +85°

DIM	CL	COLOR
-1.0		BLACK
-0.5		BLACK
1.0		BLACK
1.2		BLACK
1.2		BLACK
-0.5		BLACK
1.2		BLACK
-1.0		BLACK
0.7		BLACK
-0.5		BLUE



以过板OK为准

RECOMMENDED P.C.B LAYOUT (COMPONENT SIDE)
FOR P.C.B THICKNESS:1.20

3	铁壳	SPCC	Au/Ni Plated
2	端子	C2680	Au/Tin Plated
1	塑胶	LCP/BLACK/BLUE	UL 94V-0
NO.	PART NAME	DESCRIPTION	REMARK



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: VGA超薄短体 正向CH=-1.2~1.2
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW18-VGA15B-XXXB
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.
	UNIT: mm [inch]	DRAW NO: HYC-2604271439	SHEET NO. 1 OF 1