








未注公差/General tolerances(mm)													
0	>3	>6	>10	>18	>30	>50	>80	>120	>180	>250	>315	>400	>500
~3	~6	~10	~18	~30	~50	~80	~120	~180	~250	~315	~400	~500	
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50



REV	ECN	DESCRIPTION	DRFT	DATE



PCB Layout



(Color):GN:(Green), BK:(Black), BU:(Blue), RD:(Red), GY:(Gray)  
OG:(Orange), WT:(White), YL:(Yellow), CR:(Clear)

UL 标准/UL Standard:	
额定电压/电流/Rated Voltage(V)/Current(A)	300/20
IEC 标准/IEC Standard:	
额定电压/电流/Rated Voltage(V)/Current(A)	600/32
额定脉冲电压(KV)/Rate Impulse Voltage(KV)	/
螺丝扭矩/Torque Tightening(N·m/Lb.in)	M4/1.2
线径范围(硬线和软线)/Wire Range(rigid and flexible)(mm <sup>2</sup> /AWG)	4.0/22~10
间距/Pitch(mm)/线数范围/Poles	9.5/02~24
使用温度范围/Operating temperature(°C)	-40~+105
符合RoHS环保要求/Conform to RoHS	Yes

Cover	PC	UL94V-2
Screw	M4 Steel	Ni Plated
Pin header	Copper alloy	Sn Plated
Housing	PA66	UL94V-0
NAME OF PART	MATERIAL	NOTES

MAT NO.:	/	 宁波地博电气有限公司 NINGBO DORABO ELECTRIC CO., LTD		
STATUS:	/			
APPD: J.Ting Chen 2022.11.26	NAME:	DBT50G-9.5-XXP-C-P		
CHKD: Duck Mao 2022.11.26				
DRFT: Steven Lu 2022.11.26	DRAWING NO.:	/	REV	M1
SIZE: A4                  mm (inch)	TYPE: CUSTOMER_DRAWING	SCALE: 1:1	SHEET	1/1