








性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜, 触点镀金3U"

规格型号	DIM A	DIM B	DIM C
HYCW-BB3P3080D-50	8.0±0.15	5.9±0.3	6.9±0.3
HYCW-BB3P3090D-50	9.0±0.15	6.9±0.3	7.9±0.3
HYCW-BB3P30100D-50	10.0±0.15	7.9±0.3	8.9±0.3



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5" UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 3.0PH 3P 侧压电池座 5.0柱	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2604131601
			SHEET NO.	1 OF 1