









RECOMMENDED PCB LAYOUT

TOP VIEW (.XX±0.05)

Pin数	PART NO.	DIM A
2Pin	HWCW-BA2P2017	4.0
3Pin	HWCW-BA3P2017	6.0
4Pin	HWCW-BA4P2017	8.0
5Pin	HWCW-BA5P2017	10.0
6Pin	HWCW-BA6P2017	12.0
7Pin	HWCW-BA7P2017	14.0
8Pin	HWCW-BA8P2017	16.0

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃


塑件(材质): LCP

接触点(材质): 磷铜, 触点镀金3U",

使用寿命: 5000次以上



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.* ±2* X.X* ±0.5*		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.0PH 1.7H 正压电池座	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2020060453	
			SHEET NO.	1 OF 1	