








RECOMMENDED PCB LAYOUT
TOP VIEW (.XX±0.05)



PART NO.	DIM A	DIM B
HYCW-BA5P2524D-110	2.4	4.30±0.2
HYCW-BA5P2530D-110	3.0	4.90±0.2
HYCW-BA5P2535D-110	3.5	5.40±0.2



性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜、触点镀金3U



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.5PH 5P 正压电池座 11柱	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-202006061009
			SHEET NO.	1 OF 1