









RECOMMENDED PCB LAYOUT
TOP VIEW (. XX ± 0.05)

规格型号	DIM A	DIM B
HYCW-BF2P3519D-50	7.0	5.0
HYCW-BF3P3519D-85	10.5	8.5
HYCW-BF4P3519D-120	14.0	12.0
HYCW-BF5P3519D-155	17.5	15.5
HYCW-BF6P3519D-190	21.0	19.0
HYCW-BF7P3519D-225	24.5	22.5
HYCW-BF8P3519D-260	28.0	26.0

性能:

额定电流: 5.0A

额定电压: 30V

耐电压: 500V

接触电阻: 30m Ω MAX

绝缘电阻: 500M Ω

工作温度: -55 $^{\circ}$ C ~ +125 $^{\circ}$ C

使用寿命: 10000次以上

塑件(材质): LCP黑色

接触点(材质): 黄铜C2680, 接触面镀金3U''



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X.' $\pm 2'$ X.X' $\pm 0.5'$ UNIT: mm [inch] SCALE: 1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 3.5PH 1.9H 母座有柱	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2604131642
			SHEET NO.	1 OF 1