









RECOMMENDED PCB LAYOUT

TOP VIEW (. XX±0.05)

性能:

额定电流: 5.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -40℃~+105℃

塑件(材质): LCP黑色

接触点(材质): 铜合金, 触点镀金3U",



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ±0.30

X.XX ±0.25

X.XXX ±0.15

X" ±2" X.X" ±0.5"



UNIT: mm [inch]

SCALE:1:1

SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

4.25PH 6.2H 3P 侧压电池座 插件脚

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW-BB3P42562-C

MOLD NO.

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2604141433

SHEET NO.

1 OF 1