








RECOMMENDED PCB LAYOUT
TOP VIEW(. XX±0.05)

PART NO.	DIM A	DIM B
HYCW-BA4P2524	2.4	4.30±0.2
HYCW-BA4P2530	3.0	4.90±0.2
HYCW-BA4P2535	3.5	5.40±0.2



性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜, 触点镀金3U"



深圳市华宇创精密电子有限公司


TOLERANCE:

X.X ±0.30

X.XX ±0.25

X.XXX ±0.15

X' ±2" X.X' ±0.5"



UNIT: mm [inch]

SCALE:1:1

SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

2.5PH 4P 正压电池座

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

SEE TABLE

MOLD NO.

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-202006051223

SHEET NO.

1 OF 1