








RECOMMENDED PCB LAYOUT
TOP VIEW (.XX±0.05)

性能:

额定电流: 3.0A

额定电压: 60V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -55℃~+125℃

使用寿命: 10000次以上

塑件(材质): PA9T

接触点(材质): 黄铜C2680, 触点镀金3U



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.54PH 1.27H 6P 母座有柱
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-BF6P254127D-127
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2604131031
			SHEET NO. 1 OF 1