









RECOMMENDED PCB LAYOUT  
TOL:(±0.05)

性能:

额定电流: 5.0A

额定电压: 30V

耐电压: 500V

接触电阻: 30mΩ Max

绝缘电阻: 500MΩ Min

工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜, 触点镀金3U",

使用寿命: 5000次以上



深圳市华宇创精密电子有限公司

|                                                                            |                    |                      |                                           |
|----------------------------------------------------------------------------|--------------------|----------------------|-------------------------------------------|
| TOLERANCE:<br>X.X ±0.30<br>X.XX ±0.25<br>X.XXX ±0.15<br>X.' ±2" X.X' ±0.5" | DRAWN BY :<br>陈一鸣  | DATE :<br>2014-02-23 | PART NAME:<br>4.25PH 4.75H 2P 正压电池座有柱 防浪P |
|                                                                            | CHECKED BY:<br>马跃  | DATE :<br>2014-02-23 | PART NO.<br>HYCW-BA2P425475DF-79          |
| <br>UNIT: mm [inch]<br>SCALE:1:1 SIZE: A4                                  | APPROVED BY:<br>邱敏 | DATE :<br>2014-02-23 | MOLD NO.                                  |
|                                                                            |                    |                      | DRAW NO:<br>HYC-2604141201                |
|                                                                            |                    |                      | SHEET NO.<br>1 OF 1                       |