









RECOMMENDED PCB LAYOUT
TOP VIEW (.XX±0.05)

PART NO.	DIM A	DIM B
HYCW-BA3P3524-C	2.4	4.35±0.25
HYCW-BA3P3535-C	3.5	5.45±0.25

性能:

额定电流: 5.0A

额定电压: 24V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP E130I, 耐高温260℃

弹片(材质): 磷青铜C5210, 触点镀金3U

按压寿命: 5000次以上



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ±0.30
X.XX ±0.25
X.XXX ±0.15

X.* ±2° X.X° ±0.5°



UNIT: mm [inch]

SCALE:1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

3.5PH 3P 正压电池座 插件脚

CHECKED BY:

马跃

DATE :

2014-02-23

APPROVED BY:

邱敏

DATE :

2014-02-23

PART NO.

SEE TABLE

MOLD NO.

DRAW NO:

HYC-2604140914

SHEET NO.

1 OF 1