






RECOMMENDED PCB LAYOUT
TOL:(±0.05)



HYCW-BB8P2546-C	20.00	17.50	15.00
HYCW-BB7P2546-C	17.50	15.00	12.50
HYCW-BB6P2546-C	15.00	12.50	10.00
HYCW-BB5P2546-C	12.50	10.00	7.50
HYCW-BB4P2546-C	10.00	7.50	5.00
HYCW-BB2P2546-C	5.00	2.50	0
规格型号	A	B	C

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP黑色

接触点(材质): 磷青铜, 触点镀金3U"



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.5PH 4.6H 侧压电池座	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2604101438
			SHEET NO.	1 OF 1