








Pin数(N)	PART NO.	DIM A	DIM B	DIM C
3Pin	HYCW-BA3P425475DF-42	12.75	4.25	8.5
4Pin	HYCW-BA4P425475DF-85	17.0	8.5	12.75
5Pin	HYCW-BA5P425475DF-127	21.25	12.75	17.0
6Pin	HYCW-BA6P425475DF-170	25.5	17.0	21.25

性能:

额定电流: 5.0A

额定电压: 30V

耐电压: 500V

接触电阻: 30mΩ Max

绝缘电阻: 500MΩ Min

工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜, 触点镀金3U",

使用寿命: 5000次以上



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X" ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 4.25PH 4.75H 正压电池座有柱 防浪P	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2604141422
				SHEET NO.	1 OF 1