







性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜镀金

使用寿命: 3000次以上

PART NO.	DIM A	DIM B	DIM C
HYCW-BB3P2538D-25	9.0	5.0	2.5
HYCW-BB4P2538D-50	11.5	7.5	5.0
HYCW-BB5P2538D-75	14.0	10.0	7.5
HYCW-BB6P2538D-100	16.5	12.5	10.0
HYCW-BB8P2538D-150	21.5	17.5	15.0



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X" ±0.5" UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.5PH 3.8H 侧压电池座 带柱	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2505090953
			SHEET NO.	1 OF 1