









RECOMMENDED PCB LAYOUT
TOP VIEW(.XX±0.05)

HYCW-BB6P2530L-C190	18.00	12.50	16.90
HYCW-BB5P2530L-C190	15.50	10.00	14.40
HYCW-BB4P2530L-C190	13.00	7.50	11.90
HYCW-BB3P2530L-C190	10.50	5.00	9.40
HYCW-BB2P2530L-C190	8.00	2.50	6.90
PART NO	DIM A	DIM B	DIM C

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ 以内

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

使用寿命: 3000次以上

塑件(材质): LCP(黑色) UL94-V0

接触点(材质): 锡磷青铜, 触点镀金3U",
焊脚镀雾锡80U"以上, 镍底30U"以上

固定片(材质): 黄铜C2680,
镀全雾锡80U"以上, 镍底30U"以上

环保要求: 符合ROHS限值。



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.X' ±2" X.X" ±0.5"	DRAWN BY :	DATE :	PART NAME:	
	陈一鸣	2014-02-23	2.5PH 3.0H 沉板 侧压电池座	
	CHECKED BY:	DATE :	PART NO.	SEE TABLE
	马跃	2014-02-23	MOLD NO.	
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY:	DATE :	DRAW NO:	HYC-2604091539
	邱敏	2014-02-23	SHEET NO.	1 OF 1