









RECOMMENDED PCB LAYOUT
TOP VIEW (.XX±0.05)

Pin数	PART NO.	DIM A	DIM B	DIM C
2Pin	HYCW-BA2P2034-C	4.0	2.0	
3Pin	HYCW-BA3P2034-C	6.0	4.0	2.0
4Pin	HYCW-BA4P2034-C	8.0	6.0	4.0
5Pin	HYCW-BA5P2034-C	10.0	8.0	6.0
6Pin	HYCW-BA6P2034-C	12.0	10.0	8.0
7Pin	HYCW-BA7P2034-C	14.0	12.0	10.0
8Pin	HYCW-BA8P2034-C	16.0	14.0	12.0

性能:

额定电流: 3.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜, 触点镀金3U",

使用寿命: 5000次以上



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.* ±2* X.X* ±0.5*	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.0PH 3.4H 正压电池座	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2604081459
	SCALE:1:1	SIZE: A4	SHEET NO.	1 OF 1