









PART NO.	DIM A	DIM B	DIM C
HYCW-BB3P2038D	7.50	4.0	2.0
HYCW-BB4P2038D	9.50	6.0	4.0
HYCW-BB5P2038D	11.5	8.0	6.0
HYCW-BB6P2038D	13.5	10.0	8.0

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜, 镀金3U

使用寿命: 3000次以上



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2° X.X' ±0.5° UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.0PH 3.8H 侧压电池座 有柱	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2604081535
			SHEET NO.	1 OF 1