











RECOMMENDED PCB LAYOUT
TOL:(± 0.05)

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30m Ω MAX

绝缘电阻: 500M Ω

工作温度: -40 $^{\circ}$ C~+125 $^{\circ}$ C

塑件(材质): LCP E130i(黑色) UL94-V0 E106764

接触点(材质): 锡磷青铜, 触点镀金3U", 焊脚镀锡100U"

固定片(材质): 黄铜C2680, 镀全雾锡100U"



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X." ± 2 " X.X" ± 0.5 "	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.5PH 6.7H 4P 正压电池座 有柱 弹高2.3
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-BA4P2567D-50-23
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO. DRAW NO: HYC-2604101643
			SHEET NO. 1 OF 1