







PART NO.	A	B	C
HYCW03-BB3P2554D-68	5.4	3.8	4.6
HYCW03-BB3P2560D-68	6.0	4.4	5.2
HYCW03-BB3P2565D-68	6.5	4.9	5.7
HYCW03-BB3P2570D-68	7.0	5.4	6.2
HYCW03-BB3P2575D-68	7.5	5.9	6.7
HYCW03-BB3P2580D-68	8.0	6.4	7.2



性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜, 镀金



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5" UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.5PH 3P 侧压式电池座 带柱	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
	APPROVED BY: 柯南	DATE : 2014-02-23	DRAW NO:	HYC-BA171821601
			SHEET NO.	1 OF 1