






RECOMMENDED PCB LAYOUT
TOL: (±0.05)

HYCW-BC10P2053DW	20.50	18.00	19.90
HYCW-BC9P2053DW	18.50	16.00	17.90
HYCW-BC8P2053DW	16.50	14.00	15.90
HYCW-BC7P2053DW	14.50	12.00	13.90
HYCW-BC6P2053DW	12.50	10.00	11.90
HYCW-BC5P2053DW	10.50	8.00	9.90
HYCW-BC4P2053DW	8.50	6.00	7.90
HYCW-BC3P2053DW	6.50	4.00	5.90
HYCW-BC2P2053DW	4.50	2.00	3.90
Be filled	DIMA	DIMB	DIMC

性能:

额定电流: 5.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩMAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP 黑色

耐高温: 260度

接触点(材质): 黄铜, 接触面镀金1U"



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X." ±2" X.X" ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.0PH 刀式电池座90° DIP公座	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2604081636
			SHEET NO.	1 OF 1