








RECOMMENDED PCB LAYOUT
TOP VIEW (.XX±0.05)

PART NO.	DIM A	DIM B	DIM C
HYCW-BB4P2554-C	5.4	3.8	4.4
HYCW-BB4P2560-C	6.0	4.4	5.0
HYCW-BB4P2565-C	6.5	4.9	5.5
HYCW-BB4P2570-C	7.0	5.4	6.0
HYCW-BB4P2575-C	7.5	5.9	6.5
HYCW-BB4P2580-C	8.0	6.4	7.0

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

使用寿命: 3000次以上

塑件(材质): LCP(黑色) UL94-V0

接触点(材质): 锡磷青铜C5210, 触点镀金3U",
焊脚镀锡80U"以上, 镍30以上

固定片(材质): 黄铜C2680,
镀全雾锡80U"以上, 镍底30U"以上

环保要求: 符合ROHS限值。

弹片工作行程: 建议压缩尺寸为1.15mm-1.35mm



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ±0.30

X.XX ±0.25

X.XXX ±0.15

X" ±2° X.X" ±0.5°

UNIT: mm [inch]

SCALE: 1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

2.5PH 4P 侧压电池座

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

SEE TABLE

MOLD NO.

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2604101517

SHEET NO.

1 OF 1