






RECOMMENDED PCB LAYOUT  
TOL: (±0.05)

|                   |       |       |       |
|-------------------|-------|-------|-------|
| HWCW03-BM12P2025D | 26.00 | 22.00 | 25.40 |
| HWCW03-BM10P2025D | 22.00 | 18.00 | 21.40 |
| HWCW03-BM8P2025D  | 18.00 | 14.00 | 17.40 |
| HWCW03-BM7P2025D  | 16.00 | 12.00 | 15.40 |
| HWCW03-BM6P2025D  | 14.00 | 10.00 | 13.40 |
| HWCW03-BM5P2025D  | 12.00 | 8.00  | 11.40 |
| HWCW03-BM4P2025D  | 10.00 | 6.00  | 9.40  |
| HWCW03-BM3P2025D  | 8.00  | 4.00  | 7.40  |
| HWCW03-BM2P2025D  | 6.00  | 2.00  | 5.40  |
| Be filled         | DIMA  | DIMB  | DIMC  |



性能:

额定电流: 1.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩMAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP 黑色

耐高温: 260度

接触点(材质): 磷青铜, 接触面镀金1U"



深圳市华宇创精密电子有限公司

|                                                                            |                    |                      |                                |                |
|----------------------------------------------------------------------------|--------------------|----------------------|--------------------------------|----------------|
| TOLERANCE:<br>X.X ±0.30<br>X.XX ±0.25<br>X.XXX ±0.15<br>X.' ±2' X.X' ±0.5' | DRAWN BY :<br>陈一鸣  | DATE :<br>2014-02-23 | PART NAME:<br>2.0PH 刀式电池座 母座带柱 |                |
|                                                                            | CHECKED BY:<br>马跃  | DATE :<br>2014-02-23 | PART NO.                       | SEE TABLE      |
| UNIT: mm [inch]<br>SCALE:1:1 SIZE: A4                                      | APPROVED BY:<br>邱敏 | DATE :<br>2014-02-23 | MOLD NO.                       |                |
|                                                                            |                    |                      | DRAW NO:                       | HYC-2604081710 |
|                                                                            |                    |                      | SHEET NO.                      | 1 OF 1         |