








RECOMMENDED PCB LAYOUT
TOP VIEW (.XX±0.05)

PART NO.	DIM A	DIM B	DIM C
HWCW-BB8P2554-C	5.4	3.8	4.4
HWCW-BB8P2560-C	6.0	4.4	5.0
HWCW-BB8P2565-C	6.5	4.9	5.5
HWCW-BB8P2570-C	7.0	5.4	6.0
HWCW-BB8P2575-C	7.5	5.9	6.5
HWCW-BB8P2580-C	8.0	6.4	7.0

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

使用寿命: 3000次以上

塑件(材质): LCP(黑色) UL94-V0

接触点(材质): 锡磷青铜, 触点镀金3U",
焊脚镀锡80U"以上, 镍30U"以上


固定片(材质): 黄铜C2680,
镀全雾锡80U"以上, 镍底30U"以上

环保要求: 符合ROHS限值。

弹片工作行程: 建议压缩尺寸为1.1mm-1.3mm



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.5PH 8P 侧压电池座	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2604101553
				SHEET NO.	1 OF 1