









RECOMMENDED PCB LAYOUT
TOP VIEW (.XX±0.05)

规格型号	DIM A	DIM B
HYCW-BF2P127094	3.05	1.27
HYCW-BF3P127094	4.32	2.54
HYCW-BF4P127094	5.59	3.81
HYCW-BF5P127094	6.86	5.08
HYCW-BF6P127094	8.13	6.35

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -55℃~+125℃

使用寿命: 5000次以上

塑件(材质): LCP黑色 耐高温260度

接触点(材质): 黄铜C2680, 接触面镀金3U"



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2' X.X' ±0.5' UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 1.27PH 0.94H 母座 无柱	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2603271650
			SHEET NO.	1 OF 1