








RECOMMENDED PCB LAYOUT
TOP VIEW (.XX±0.05)



PART NO.	DIM A	DIM B
HYCW-BA4P2540D-85	4.0	5.90±0.2
HYCW-BA4P2545D-85	4.5	6.40±0.2
HYCW-BA4P2555D-85	5.5	7.40±0.2



性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜, 触点镀金3U"



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.5PH 4P 正压电池座 8.5柱	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-202006051747
			SHEET NO.	1 OF 1