








RECOMMENDED PCB LAYOUT
TOL:(±0.05)

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -40℃ ~ +85℃

塑件(材质): LCP 黑色

接触点(材质): 铜合金

规格型号	DIM A	DIM B
HYCW-BB7P3072-C	7.2	5.5
HYCW-BB7P3065-C	6.5	4.8
HYCW-BB7P3050-C	5.0	3.3
HYCW-BB7P3046-C	4.6	2.9

 深圳市华宇创精密电子有限公司			
TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5"  UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 3.0PH 7P 侧压电池座 插件脚
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. SEE TABLE
	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2604131536
			SHEET NO. 1 OF 1